






CARLO GAVAZZI
Automation Components



Solutions for Plastics Machinery



Solutions for Plastics Machinery


With more than 40 years
expertise in designing
and building components
for plastics machinery,
Carlo Gavazzi can
provide fully customized
solutions, regardless of
your requirements.





MEMBER





Modular Power Quality Analyzers

WM23 96 Series

- 96 x 96 x 140mm for panel mounting
- 3-phase power quality analyzer with back lit LCD display for measurement of systems and phase variables
- Up to 830VAC (*phase to phase*), up to 20kV (*VT connection*) and up to 5,000A (*CT connection*)
- Instantaneous variable: 4 x 3 ½ digits
- Accuracy: 0.5% reading (A, V)
- IP65 protection
- CE, UL and CSA



Power Quality Transducers

PQT90 Series

- 90 x 90 x 138mm for DIN rail mounting
- 32 bit microprocessor based power quality transducer for measurement of all instantaneous variables
- SMS messages
- Energy, water and gas meter
- 2MB Memory and real time clock
- Class 0.5 (A, V)
- IP20 protection
- CE, UL and CSA



RJCS Series single phase solid state relays with integrated current monitoring




IA, CA, PA and UA Series inductive, capacitive, photoelectric and ultrasonic sensors

RJ Series Solitron-Mini single phase solid state relays (also offered in wider housings for up to 90 amps and two or three pole switching)



SMS and CLS Series safety magnetic sensors with magnet



Our Product Range



Compact Power Transducers

CPT DIN Series


- 45 x 83 x 98.5mm for DIN rail mounting
- Power analyzer and energy meter for measurement of all instantaneous variables
- Up to 2 alarm or pulse outputs or up to 2 analog outputs
- Dupline bus
- RS232/485/422 (Modbus)
- Class 0.5 (A, V)
- IP20 protection
- CE, UL and CSA



Current Monitoring Relays

DIA53 Series

- 81.5 x 17.5 x 67mm for DIN rail mounting
- Self-powered 1-phase over current monitoring relay with 12mm hole for insulated current carrying wire
- Set point adjustment for up to 20, 50 or 100 AAC
- 100mA normally open transistor output
- 0.5% repeatability
- IP20 protection
- CE, UL and CSA



Chassis Mount Solid State Relays

RM1A Single Phase Series

- 58.2 x 44.8 x 28.8mm
- Zero switching, with other types available
- Up to 100AAC output at up to 660VAC
- IP20 protection
- CE, UL and CSA

RZ3A Three Phase Series

- 73.5 x 103 x 41mm
- Zero switching
- Up to 75AAC output at up to 660VAC
- Optional over-temperature protection, transistor alarm output and red LED alarm status indicator
- IP20 protection
- CE, UL and CSA



SSRs with Integrated Heat Sinks

RJ Mini Series

- 80 x 22.5 x 103mm
- 1-phase solid state relays (2 and 3 pole versions also offered in wider housings)
- Zero switching or instant-on
- Up to 30AAC output at up to 660VAC (larger sizes available in wider housings)
- IP20 protection
- CE, UL and CSA

RJCS Series

- 81.7 x 45 x 103mm
- 1 phase solid state relays
- Integrated current monitoring with local or remote setup
- Zero switching
- Up to 50AAC output at up to 660VAC
- IP20 protection
- CE, UL and CSA



Fast-Connect Solid State Relays

RX ThyRex Series

- 76 x 22.5 x 56mm
- 1-phase solid state relays
- Zero switching
- Up to 32AAC output at up to 550VAC
- Screw, spring or fast-on terminal connection options decrease installation time
- IP20 protection
- CE, UL and CSA

www.GavazziOnline.com/Plastics

Designed to Market Requirements

Dedicated application engineering teams design special products upon request from the customer.

Solution to Applications Challenges

Carlo Gavazzi's individual product ranges complement one another, thereby offering the customer all the advantages of a synergistic range of products in terms of application and availability.

Guaranteed Reliability

Each product group is designed and manufactured in a center of excellence to assure that each individual product is the best in its field. Carlo Gavazzi products are subject to stringent quality tests to guarantee they exceed the performance we specify.

Visit www.GavazziOnline.com/Plastics to download data sheets or to check price and delivery

for Plastics Machinery



Inductive Proximity Sensors

IA Series

- M5, M8, M12, M18 and M30 threaded diameters
- Sensing ranges up to 22mm
- NAMUR, transistor, SCR or analog output
- Thermoplastic polyester, stainless steel or nickel-plated brass housings
- 2m PVC cable or M8/M12 plug
- IP67 protection
- CE, UL and CSA



Capacitive Proximity Sensors

CA / EC Series

- M12, M18, and M30 threaded diameters
- Rectangular flat-pack housings also offered
- Sensing ranges up to 30mm
- Transistor or SCR output
- Thermoplastic polyester, stainless steel, Teflon, polypropylene, or PVC housings
- 2m PVC cable or M12 plug
- IP67 or IP68 protection
- High temperature models (up to 356°F)
- Teach-in models with push button programming
- UL, CSA, and CE




Photoelectric and Ultrasonic Sensors

PA18/Ex18 Series

- Diffuse reflective: 400mm
- Retro-reflective: 3m
- Polarized retro-refl.: 2m
- Through beam: 10 or 20m
- M18 diameter
- Transistor or SCR output
- 2m PVC cable or M12 plug
- IP67 protection
- CE, UL and CSA

UA12/18/30 Series

- Ultrasonic sensors with integrated amplifier providing a transistor and/or analog output and integrated amplifier; up to 3,500mm range (138")
- M12, M18 and M30 diameters
- Transistor or analog output
- 2m PVC cable or M12 plug connector
- IP67 protection
- CE mark



Safety Light Curtains

SB4 Series

- Light curtains to protect both employees and machinery
- Total or partial muting, override and automatic or manual reset
- 35 x 40mm in lengths from 256 - 1,726mm (10 - 68")
- 24VDC supply with two PNP transistor outputs
- M12 4 pole plug connection for transmitter and M12 8 pole plug connection for receiver
- Aluminum housing
- IEC-61496-2 environment light rejection
- IP65 protection
- CE, UL and CSA



Safety Modules

NA1/3 and NL1/3 Series

- Safety modules for gate and emergency stop (NA) and light curtain (NL)
- Safety category 4
- 3 normally open safety outputs
- 24VAC/DC, 110VAC or 230VAC power supply (NA), 24 VAC/DC power supply (NL)
- < 30mS response time
- IP40 protection for housing and IP20 protection for terminals
- CE, UL and CSA

- Panel building can be a time-intensive operation as each solid state relay needs to be individually mounted and wired. The ThyRex Series is an innovative fast-connect SSR from Carlo Gavazzi. Mounting and wiring are done simultaneously, thus speeding up the installation process.
- In the blow moulding process, subtle temperature control is key in determining the quality of the final outcome. SSRs offer a greater degree of control over the process than electromechanical relays or contactors, as they don't have moving parts and allow for frequent switching of loads.

- With their integrating thyristors and direct copper bonded ceramic, Carlo Gavazzi SSRs provide an extremely robust switching solution for blown film extrusion and injection moulding technologies. SSRs can help maximize plant up-time and minimize loss of production.
- By using an ultrasonic sensor to check film loop tension in blown film machinery, film breakage is prevented and interruptions in the production cycle are minimized.
- Ultrasonic sensors can continuously monitor the diameter of the blown film reel. Early warning signals alert technicians when a reel will need replacing, ensuring greater control over the production process.



Safety Magnetic Sensors

SMS Series Sensors

- 88 x 25 x 13mm
- Normally open or closed output
- Up to 100VAC switching
- 250mA maximum output
- Up to 5VA switching power
- Rugged plastic housing
- IP65 protection

CLS Magnetic Units

- 88 x 25 x 13mm
- Rugged plastic housing
- IP65 protection



Dupline Channel Generators

G3800 Series


- 77 x 144 x 70mm for DIN rail mounting
- Modbus interface with built-in GSM or external radio modem.
- Up to 32 controllers can be networked together via RS485 or Ethernet via a converter module
- Selectable number of channels
- 10-30VDC or 115/230VAC power supply
- IP20 protection
- CE mark



NL1 Series safety light curtain modules

NA1 Series safety gate and emergency stop modules

CA Series capacitive proximity sensors featuring Tripleshield protection, providing protection against static electricity, inverters, mobile phones, wire conducted noise, as well as humidity, dirt and moisture



CPT DIN Series power analyzer and energy meter



G3800 Series Dupline Modbus interface


RX ThyRex Series single phase solid state relays




DIA53 Series over current monitoring relays



PQT90 Series power quality transducer



The Complete Product Package



Sense
 Inductive Proximity Sensors
 Tripleshield™ Capacitive Sensors
 Photoelectric Sensors
 Inductive Loop Detectors
 Ultrasonic Sensors
 Level Sensors
 Limit Switches
 Magnetic Switches



Switch
 Solid State Relays
 Contactors and Overloads
 Manual Motor Starters
 Motor Controllers
 Variable Frequency Drives
 Electromechanical Relays
 Pilot Devices
 Cam Switches
 Rotary Disconnects



Control
 Energy Management
 Digital Panel Meters
 PID Controllers
 Time Delay Relays
 Current Monitoring Relays
 Voltage Monitoring Relays
 Three Phase Monitoring Relays
 Signal Conditioners
 Current Transformers
 Enclosures



Safety
 Light Curtains
 Control Modules
 Interlock Switches
 Mat Systems
 Magnetic Sensors



Dupline
 Dupline Field & Installation Bus
 Building Automation Systems
 Elevator Systems

A Global Force in Industrial Automation

CARLO GAVAZZI has a multitude of sales offices spanning North America (not to mention our hundreds of distributors). Therefore, we can be viewed as "your local automation resource" - assisting you every step of the way in finding the proper solution for your various application requirements. Naturally, our job is greatly simplified as we have such a vast range of solutions to offer you via our comprehensive product package.

Our worldwide sales offices make us an ideal business partner, especially for manufacturers of exported machinery, as our products are available locally and they are CE marked.

USA
CARLO GAVAZZI INC.
 750 Hastings Lane
 Buffalo Grove, IL 60089
 Tel 847.465.6100
 Fax 847.465.7373
Sales@CarloGavazzi.com

CANADA
CARLO GAVAZZI (CANADA) INC
 2660 Meadowvale Boulevard
 Mississauga, Ontario L5N 6M6
 Tel 905.542.0979, Fax 905.542.2248
CARLO GAVAZZI (CANADA) LTÉE
 3777 Boulevard du Tricentenaire
 Montréal, Quebec H1B 5W3
 Tel 514.644.2544, Fax 514.644.2808
Gavazzi@CarloGavazzi.com

Regional / Area Sales Office
 District Sales Office

Argentina • Australia • Austria • Bahrain • Belgium • Bolivia • Bosnia • Brazil • Brunei • Bulgaria • Canada
 Chile • China • Columbia • Croatia • Cyprus • Czech • Denmark • Dominican Republic • Egypt • Estonia
 Finland • France • Germany • Greece • Hungary • Hong Kong • Iceland • India • Indonesia • Iran • Ireland • Italy • Japan
 Jordan • Kenya • Korea • Kuwait • Lebanon • Malaysia • Malta • Maroc • Mauritius • Mexico • Netherlands
 New Zealand • Norway • Pakistan • Papua New Guinea • Paraguay • Peru • Philippines • Poland
 Portugal • Qatar • Romania • Russia • Saudi Arabia • Serbia • Singapore • Slovakia • Slovenia • South Africa
 Spain • Sultanate of Oman • Sweden • Switzerland • Taiwan • Thailand • Tunisie • Turkey
 Ukraine • United Arab Emirates • United Kingdom • Uruguay • United States of America • Venezuela • Vietnam

Plastic Solutions Brochure 6/06

Your Authorized Distributor:

CARLO GAVAZZI
 Automation Components

USA Phone: 847.465.6100 Fax: 800.222.2659

Canada Ontario: 905.542.0979 Quebec: 514.644.2544

Website www.GavazziOnline.com

Email Sales@CarloGavazzi.com

CARLO GAVAZZI

Visit our website for downloadable data sheets,
 brochures & pricing: www.GavazziOnline.com